

MICAPS ECOHDMI1080P

C-mount USB CMOS Cameras
SONY STARVIS CMOS Sensor



The ECOHDMI1080P series camera is designed specifically for capturing digital images from stereo microscopes and biological microscopes equipped with an HDMI interface.

Features

- Sony Starvis back illuminated CMOS sensor
- FHD HDMI video outputs
- SD card for the captured image and video storage
- Embedded XCamView for the control of the camera
- With strong ISP and other related processing functions
- Rolling Shutter

Applications

- Scientific research, education (teaching, demonstration and academic exchanges)
- Digital laboratory, medical research
- Industrial visual (PCB examination, IC quality control)
- Medical treatment (pathological observation)
- Food (microbial colony observation and counting)
- Aerospace, military (high sophisticated weapons)

Model No.	Sensor & Size(mm)	Pixel(μm)	G Sensitivity Dark Signal	FPS/Resolution	Binning	Exposure
ECOHDMI1080P	Sony IMX307(C) 1/2.8"(5.57x3.13)	2.9x2.9	1300mv with 1/30s	60@1920*1080(HDMI)	1X1	0.01~1000

Interface or Button	Function Description	Other Function	Function Description
HDMI	Comply with HDMI1.4 standard. 1080P format video output for standard FHD monitor	Video Saving	Video format: 2M(1920*1080) H264 encoded MP4 file Video saving frame rate: 50~60fps (related with SD card performance)
SD	Comply with SDIO3.0 standard and SD card could be inserted for video and images storage	Image Capture	2M (1920*1080) JPEG image in SD card
LED	LED status indicator	Measurement Saving	Measurement information saved in different layer with image content Measurement information is saved together with image content in burn in mode
DC12V	Power adapter connection (12V/1A)	ISP	Exposure(Automatic / Manual Exposure) / Gain, White Balance(Manual / Automatic / ROI Mode), Sharpening, 3D Denoise, Saturation Adjustment, Contrast Adjustment, Brightness Adjustment, Gamma Adjustment, Color to Gray, 50HZ/60HZ Anti-flicker Function
USB Mouse	Connect USB mouse for easy operation with embedded MicroCamView software	Image Operation	Zoom In/Zoom Out, Mirror/Flip, Freeze, Cross Line, Overlay, Embedded Files Browser, Video Playback, Measurement Function
Video Output Interface	Function Description	Embedded RTC(Optional)	To support accurate time on board
HDMI Interface	Comply with HDMI1.4 standard; 60fps@1080P	Restore Factory Settings	Restore camera parameters to its factory status
Operating Environment		Multiple Language Support	English / Simplified Chinese / Traditional Chinese / Korean / Thai / French / German / Japanese / Italian / Russian
Operating Temperature (in Centidegree)	-10~ 50		
Storage Temperature (in Centidegree)	-20~ 60		
Operating Humidity	30~80%RH		
Storage Humidity	10~60%RH		

C: Color.

LABLINK INSTRUMENTS

- Plot no. 435, Sector 2, HSIIDC Saha, Saha, Ambala (Haryana) India - 133104.
- Plot no 3-6-164/2, 2nd Street, Hyderguda Himayatnagar, Hyderabad (Telangana) India - 500029

Contact us:

Email:- info@lablinkinstruments.com
www.lablinkinstruments.com, www.micaps.com